


**elesa**  
Original design PR-PF



$b_1$	$b_2$	$b_3$	$h_1$	$h_2$	$l_1$	$l_2$	$l_3$	$F_1$ in N	$F_2$ in N
92	76	83	37	25	19	17	17,4	1800	500
137	122	128	37	25	19	17	17,4	1800	500

**Specification**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +80 °C
- Color
  - Black-gray, RAL 7021, matte finish
  - Orange, RAL 2004, matte finish
  - Gray, RAL 7035, matte finish
  - White, RAL 9002, matte finish

- **SG**
- **OR**
- **GR**
- **WS**

RoHS

**On request**

Plastic (SV), self-extinguishing



For mounting gripping trays GN 731.1 are no fixing screws required. The values of the load capacities  $F_1$  and  $F_2$  were tested with wall thickness  $s = 1.5$  mm.

see also...

	Page
GN 731 Gripping Trays (Clip-In Type)	QVX
GN 733 Gripping Trays (Screw-In Type)	QVX

**Technical Information**

Mounting Information	QVX
Plastic Characteristics	QVX

How to order

**GN 731.1-92-SG**




1  $b_1$

2 Color



### Mounting information

- 1) Drill the handle housing according to the template dimensions reported in the table.
- 2) Remove all drilling burrs before fitting the handle.
- 3) Fit the upper part of the handle into the housing.
- 4) Press onto the lower part until the handle is completely inserted.



Wall thickness <b>s</b>	for $b_1 = 92$		for $b_1 = 137$	
	<b>x</b> +0,2	<b>y</b> ±0,1	<b>x</b> +0,2	<b>y</b> ±0,1
0,7 ... 0,8	87,5	30,5	132	30,5
> 0,8 ... 1,2	87,5	30,7	132	30,7
> 1,2 ... 1,5	87,5	31,7	132	31,7
> 1,5 ... 2	87,5	31,7	132	31,7
> 2 ... 2,2	87,5	31,7	132	31,7

