



1		2						
d ₁	d ₂ H10		b ±0,2	d ₃	d ₄	l ₁	l ₂	s
32	B 14	-	11	M 4	13	37	30	2,1
36	B 15	B 16	13	M 5	13	38,5	30	2,1
42	B 18	B 20	15	M 5	13	41	30	3
48	B 22	B 25	15	M 5	13	43	45	3
55	B 28	B 30	15	M 6	13	45	45	3
60	B 32	B 35	15	M 6	13	46,5	45	4
65	B 40	-	15	M 6	13	47,5	45	4

Specification

- 3

ST
- Steel
 - Sintered
 - Black oxidized with vapor
- NI
- Stainless steel AISI 316LHC
 - Sintered
- AL
- Aluminum
 - Turned, tumbled
 - Adjustable hand levers
 - Zinc die casting
 - Powder coated
 - Black RAL 9005, textured finish
 - Screw insert and retaining screw
 - Stainless steel AISI 303
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Semi-split shaft collars GN 706.4 can safely and simply be clamped by reducing the slot height by using an adjustable hand lever and thus they act, for instance, like an end stop. This version offers great advantages especially for applications that demand new positions of the shaft collar.

The thread d₃ for sizes d₁ = 32 and 36 is designed as a through hole; for sizes d₁ = 42 and larger, it is designed as blind hole.

see also...

- Semi-Split Shaft Collars GN 706.2 (with Socket Cap Screw) → Page 1148

How to order	1	d ₁
	2	d ₂
	3	Material
GN 706.4-36-B16-AL		