



- 4 Type**
- MS** Brass pivot
 - KU** Plastic pivot (Polyacetal POM)
 - ZK** Spherical pivot

1 2 3

d ₁	d ₂	l ₁				d ₃	d ₄	d ₅	d ₆ +0,05	h ₁	h ₂	l ₂	l ₃	l ₄ ≈	
34	M 6	6	15	20	25	30	16	4	3,5	4,5	21	10,5	1	1,3	5,1
42	M 8	8	20	25	30	40	19	6	5	6,1	26	13	1,5	1,6	6,2
53	M 10	10	25	30	40	50	24	8	6,5	7,8	32	16	2	1,9	7,3

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, matte finish
- Threaded stud Stainless steel AISI 304
- Cover cap Plastic Light gray, matte finish
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Knurled screws GN 7336.5, type MS / KU with brass or plastic pivots are used when pressure dents or damage must be avoided.

Knurled screws GN 7336.5, type ZK feature a spherical pivot whose Ø d₆ is smaller than the core Ø of the thread. The version with spherical pivot is suitable for holding GN 631 / GN 631.5 thrust pads, which must be ordered separately.

The knurled screws GN 7336.5 distinguish an attractive design in combination with closed shape (no recess on the underside of the handles).

see also...

- *Thrust Pads (Plastic) GN 631* → Page 1071
- *Stainless Steel Thrust Pads GN 631.5* → Page 1071
- *Star Knobs GN 6336.10 (with Pivot)* → Page 548
- *Star Knobs GN 6336.12 (with Movable Thrust Pad)* → Page 549
- *Knurled Screws GN 421.10 (with Pivot)* → Page 638
- *Knurled Screws GN 421.12 (with Movable Thrust Pad)* → Page 639

How to order

1	d ₁
2	d ₂
3	l ₁
4	Type

GN 7336.5-42-M8-25-MS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4