



12

<b>Specification</b>		4
<b>Guide</b>		
• Steel precision casting		
- Zinc plated, blue passivated		● ZB
- Zinc plated and powder coated		
Black, RAL 9005, textured finish		● SW
• Stainless steel precision casting AISI CF-8		● NI
<b>Plunger pin</b>		
• Steel, hardened		
Zinc plated, blue passivated for ZB / SW		
• Stainless steel AISI 431, hardened for NI		
<b>Pull ring</b>		
• Steel precision casting		
Zinc plated, blue passivated for ZB / SW		
• Stainless steel precision casting AISI CF-8 for NI		
<b>Pressure spring</b>		
Stainless steel AISI 316Ti		
RoHS		
<b>Technical Information</b>		<b>Page</b>
Application examples		QVX
List of Indexing Plunger Types		QVX
Stainless Steel Characteristics		QVX

Indexing plungers GN 724.5 have a plunger pin with square cross-section, a latching surface on one side and a chamfer on the other. When the object to be secured moves towards the chamfer, the plunger pin is pushed back into the guide, allowing grooves and edges to pass over the pin. The plunger pin engages automatically in the direction of the latching surface. The latching can be released by pulling the pull ring by hand or with a cable or pull rod using a hook.

The types with rest position are used when the plunger pin should temporarily not protrude. For this purpose, the pull ring is turned sideways after the plunger pin has been retracted. The ring is held in this position by the catch recess at the top of the guide.

The dimensional tolerances between the pin and the guide have been chosen to ensure functional reliability even in roughly dimensioned applications or in the event of soiling.

There are several options for fastening. The hex mounting holes allow the use of socket cap screws ISO 4762 and hex head screws or nuts according to DIN 931 or DIN 934.

How to order		1	b
		2	s
		3	Type
		4	Material (Finish)

1234

GN 724.5-20-30-C2-NI