


- 3 Type**
- OS** Neutral, plain
 - OSS** Neutral, black anodized
 - ES** With DIN re-fill symbol, plain
 - ESS** With DIN re-fill symbol, black anodized
 - AS** With DIN drain symbol, plain
 - ASS** With DIN drain symbol, black anodized
- 4 Identification no.**
- 1** Without vent drilling
 - 2** With vent drilling

1	2										
d ₁	d ₂				d ₃ Vent drilling	d ₄	e ≈	l ₁	l ₂	s	t
19	G 1/4	M 14 x 1,5	-	-	2	M 5	17,3	15,5	8	15	8
22	G 3/8	M 16 x 1,5	-	-	2	M 5	20,8	15,5	8	18	8
26	G 1/2	M 20 x 1,5	-	-	2	M 5	24,3	16	8,5	21	8
32	G 3/4	M 26 x 1,5	M 27 x 1,5	-	2	M 5	31,2	17	9	27	8
40	G 1	M 33 x 1,5	-	-	2	M 5	37	19,5	11	32	8
50	G 1 1/4	M 40 x 1,5	M 42 x 1,5	M 42 x 2	2	M 5	47,3	21	12	41	8
60	G 1 1/2	-	-	-	2	M 5	57,7	22	13	50	8

Specification

- Aluminum
 - Type OS, ES and AS
 - Fine turned, plain
 - Type OSS, ESS and ASS
 - Fine turned, black anodized
 - Symbols laser engraved
- GN 741**
 - Temperature resistant up to **100 °C**
 - Seal
 - Ethylene propylene diene rubber (NBR)
 - Black
- GN 742**
 - Temperature resistant up to **180 °C**
 - Seal
 - Fluorine rubber (FPM / FKM)
 - Brown
- Elastomer Characteristics → Page 2158
- RoHS
- On request
 - With dipstick

Information

Threaded plugs GN 741 / GN 742 are fitted with outside diameter **d₁** to suit screw holes with BSP threads to DIN 3852.

The sealing ring is embedded in a radial recess on the flat side. This prevents the seal from being lost or squeezed out during tightening.

see also...

- Threaded Plugs GN 745 (Plastic) → Page 1584
- Threaded Plugs GN 747 (Plastic, with DIN-Re-Fill Symbol) → Page 1587
- Threaded Plugs GN 740 (Plastic, with DIN-Drain Symbol) → Page 1586
- Threaded Plugs GN 441 / GN 442 (with Catch) → Page 1599

How to order (100 °C)	1 d ₁
2 d ₂	
3 Type	
4 Identification no.	
GN 741-26-G1/2-OSS-1	

How to order (180 °C)	1 d ₁
2 d ₂	
3 Type	
4 Identification no.	
GN 742-32-M26x1,5-ES-2	