



2		3							
d ₁		d ₂	d ₃	d ₄	l ₁	l ₂	l ₃ ≈	l ₄	s
KT	NI								
16	-	M 6	10	13	41,5	12	4	15	8
18	18	M 6	10	14,5	56	13	4	19	8
22	22	M 8	14	18,5	59	14	5,2	21	11
24	24	M 10	14	18,5	74	16	5,2	27	11
25	-	M 10	16	20	84	16	5,5	30	13

Specification

Handle

- Plastic Polyamide (PA)
 - Operating temperature up to 90 °C
 - Black, matte finish
- Stainless steel AISI 303
 - Fine turned, plain

Spindle

Stainless steel AISI 303

RoHS

The design of the revolving handles GN 798.4 is characterized by their shape, consisting of two cylinders. It gives the hand an excellent grip.

see also...	Page
GN 798.5 Retractable Handles (with Hold in Both positions)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1	Material
1	2	d ₁
2	3	d ₂