




1 s ₁	2 s ₂	3 n	4 d ₁	d ₂ For screw	h ₁	h ₂	m ₁	m ₂	Grid size
30	60	8	M 10 M 12	M 8 / S 8	12	3,2	30	-	30
40	80	10	M 10 M 12	M 12 / S 12	16	8	40	-	40
45	90	10	M 12 M 14	M 12 / S 12	16	8	45	-	45
80	80	10	M 12 M 16	M 12 / S 12	16	8	40	40	40
90*	90	10	M 16 M 20	M 12 / S 12	16	8	45	45	45

* Only compatible with profile type L

Specification

Zinc die casting

Black

RoHS

6

ZS

Transport and base plates GN 80b affix attachments such as leveling feet or castors to aluminum profiles.

They are installed in the profile holes on the end faces using suitably tapped threaded holes or thread-forming screws.

see also...

GN 10b Aluminum Profiles (Profile Type Light) QVX

GN 10b Aluminum Profiles (Profile Type Heavy) QVX

Technical Information

Assembly Instructions / Profile Machining QVX

Accessory

GN 21b Central Screws QVX

How to order

1	s ₁
2	s ₂
3	n
4	d ₁
5	Type
6	Material / Color

GN 80b-45 90 10 M12-A-ZS

Assembly Instructions / Profile Machining

