



² d ₁	³ d ₂	d ₃	d ₄	l ₁	l ₂	l ₃ ≈	t
16	M 5	10	13	41,5	15	2,5	10
18	M 5	10	14,5	56	19	2,5	10
22	M 6	14	18,5	59	21	2,5	12
24	M 6	14	18,5	74	27	2,5	12
25	M 8	16	20	84	30	2,5	14

Specification

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 90 °C
- Black, matte finish

¹

KT

Spindle

- Steel
- Zinc plated, blue passivated

RoHS

The design of the revolving handles GN 798.2 is characterized by their shape, consisting of two cylinders. It gives the hand an excellent grip.

see also...

GN 798 Revolving Handles

Page

QVX

Technical Information

Plastic Characteristics

QVX

How to order

¹
GN 798.2-KT-24-M6

¹ Material

² d₁

³ d₂