



2 Bore code

K With keyway

1 3 4

d ₁	d ₂ H7 Bore	l ₁ - l ₂		d ₃	l ₃ Guide length	l ₅	t +1 Max. assembly length of the shaft	Permissible r.p.m. / torque / Determining of the size → Page 1644				
22	K 10	140-30	160-40	180-60	230-100	-	-		22	30	48	12
25	K 12	160-30	180-45	200-70	250-105	300-150	-		26	40	56	13
28	K 14	170-30	200-60	220-80	280-140	350-200	400-250		29	40	60	13
32	K 16	190-30	210-40	240-80	275-115	380-210	400-230		32	40	68	16
36	K 18	230-50	270-100	290-110	400-220	500-320	-		37	40	74	17
42	K 20	250-50	290-90	320-120	420-220	500-300	-		42	45	82	18
45	K 22	270-50	330-100	470-240	-	-	-		47	50	95	22
50	K 25	295-50	350-100	420-170	500-245	-	-		52	50	108	26
58	K 30	330-50	370-85	400-110	500-220	-	-		58	60	122	29

Specification

- Steel Plain
- Joint bearing areas / pins / bearing sleeves Case-hardened
- Keyway JS9 DIN 6885 → Page 2078
- Cross Holes GN 110.1 → Page 2081
- ISO Fundamental Tolerances → Page 2151
- RoHS

On request

- Different lengths l₁ - l₂
- Bores without keyway
- Bores with square
- Bores with hexagon
- With other or unequal bores
- Version in stainless steel (Friction bearing not rustproof)

Information

Universal joint shafts with friction bearing GN 808.2 not only join the offset between two shafts, but also enable the alignment of lengths, which depending on the overall length l₁ enables the corresponding extraction length l₂. The power transmission is achieved by two universal joints DIN 808 (Type EG) a spline shaft and a sliding sleeve.

It is important to check the accuracy when connecting the spline shaft to the sliding sleeve.

The markings → ← have to be opposite to each other. Any kind of misconnection leads to an inhomogeneous output and to a quick abrasion.

see also...

Universal Joints with Needle Bearing GN 808.3 → Page 1651

How to order

GN 808.2-50-K 25-350-100

1	d ₁
2	Bore code
3	d ₂
4	l ₁ - l ₂