

2 Type

F Solid clamping arm

1

Size	F_H in N Holding capacity	b_1	b_2	b_3	b_4	e
1000	10000	80	36	20	20	67
2000	20000	100	36	20	20	82
3000	30000	110	45	25	25	90

Size	h_1	h_2	h_3	l_1	l_2	r
1000	265	55	25	190	110	177
2000	297	65	35	220	120	202
3000	320	80	40	250	140	230

Specification

- Bearing pins and clamping lever
Steel St 60
Blackened
- Other parts
Steel St 37
- Weldable
- Blackened
- Bearing pins and rivets case-hardened
- All moving parts
Lubricated with special grease
- Solid designed plastic handle
Red, oil resistant
- RoHS

Information

Toggle clamps GN 813 are used for applications where a very high holding force is required, such as closing of foam molds.

These clamps have been designed for easy dismantling: i.e. the bearing pins are locked with circlips.

After dismantling the individual parts, they can be modified to suit individual applications.

see also...


- General Information to Toggle Clamps → Page 698

How to order

GN 813-2000-F

1 Size

2 Type



1.1
1.2
1.3
1.4



2.1
2.2
2.3
2.4

