





- 2 Identification no.**
- 1 Protection class IP 65
 - 2 Protection class IP 67



1	d_1	b	d_2 H7	d_3	l_1	l_2	l_3	m_1	m_2	m_3	Grub screw	LCD display Number of positions	Max. rpm
	Ø Linear actuator												
	25	33,5	8	19,5	34	28,5	5,5	30,5	25	22	M 4	5	1000
	30	33,5	8	19,5	34	28,5	5,5	30,5	25	22	M 4	5	1000
	40	48	12	28,5	41	34	6	40	32,5	30	M 5	6	1000
	50	48	12	28,5	41	34	6	40	32,5	30	M 5	6	1000
	60	48	14	28,5	41	34	6	40	32,5	30	M 5	6	1000

Specification

Housing

Plastic, polyamide (PA)

- Orange, RAL 2004
- Gray, RAL 7035, shiny finish
- Operating temperature 0° to 50 °C
- Oil and solvent resistant

LCD display

5 digits / 6 digits and special characters

Hollow shaft / Adapter bushing

Stainless steel AISI 304

O-ring for identification no. 2

Acrylonitrile butadiene rubber (NBR)

RoHS

OR

GR*

Electronic position indicators GN 9034 are designed for attachment to configurable linear units. They are mounted to the spindle stem of the linear actuator using an adapter bushing and a grub screw. The position indicators must be adjusted for the thread pitch and direction of the linear actuators. Power is supplied by a long-life battery.

The housing is welded by ultrasound, making it particularly sturdy, tight and compact. The foam rubber seal prevents the transmission of vibrations and acts as a seal.

Technical Information

	Page
ISO Fundamental Tolerances	QVX
IP Protection Classes	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 d_1
GN 9034-50-2-GR	2 Identification no.
	3 Color

3.8 Adjusting, Moving with Guides, Spindles and Ball Rollers

1