



b	d₁ F9	d₂	l₁	l₂	l₃	l₄	l₅	m₁	m₂	m₃	m₄
33	B 8 B 10 B 12 B 14	4,5	55	30,5	14,5	24,5	22	20	21	23,5	20

Specification

Clamping plate

Zinc die casting
Powder coated
Black, textured finish

Adjustable hand lever GN 302.1

- Handle
Zinc die casting
Powder coated
Black, RAL 9005, textured finish
- Insert / Retaining screw
Stainless steel AISI 303

RoHS

Clamping plates GN 9054.6 are used in connection with position indicators GN 9054 / GN 9154. The mounting holes support typical bore hole patterns. In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is positioned either to the right or the left.

see also...	Page
GN 9054 Position Indicators (Electronic)	QVX
GN 9154 Position Indicators (Electronic, Data Transmission via Radio Frequency)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN9054.6-33-B12

1	b
2	d ₁

