




1	2	3			
l ₁	d ₁	l ₂	d ₂	h ₁	h ₂ ≈
44*	M 6	20	10	8,5	32
63	M 6	20	10	9	40
63	M 8	25	13	13,5	44
78	M 8	25	13	14,5	52

* This size is only available in version SG.

Specification

4

Handle

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, RAL 7021, matte finish

● SG

● VDB

Serrated ring

Zinc die casting

Insert / Retaining screw

Stainless steel AISI 305

RoHS

For plastic clamp connectors, adjustable hand levers GN 911.9 replace the hexagon socket cap screws DIN 912, the clamping point or the joint axis. There are two handle lengths to choose from, depending on the thread size. The plastic used in version VDB is made from blue, visually detectable and FDA-compliant plastic granulate as per FDA CFR.21 and EU 10/2011.

Technical Information

Page

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order	1	l ₁
	2	d ₁
	3	l ₂
	4	Color
GN911.9-63-M8-25-SG		

3.7 Connecting, Assembling with Clamping and Connecting Elements

1