



- 3 Type
- E With threaded blind bore
- D With threaded through bore

1 d ₁	2 d ₂	d ₃	d ₄	b	h ₁	h ₂	t ₁ min.	t ₂
46	M 6	13	6,5	6	22,5	6	12	10
46	M 8	13	8,5	6	22,5	6	15	13
58	M 8	16	8,5	7	26,5	7	15	13
58	M 10	16	10,5	7	26,5	7	18	16

Specification

- Stainless steel

Precision casting AISI CF-8

Matte shot-blasted
- MT
- [Stainless Steel Characteristics → Page 2166](#)
- [RoHS](#)

Information

- see also...
- [Stainless Steel Wing Nuts GN 432 → Page 621](#)

• [Stainless Steel Wing Nuts GN 434 → Page 620](#)

• [Stainless Steel Three-Lobe Knobs GN 5345 → Page 592](#)

• [Stainless Steel Hand Knobs DIN 6335 → Page 582](#)

How to order	1 d ₁
	2 d ₂
	3 Type
	4 Finish
GN834-46-M8-E-MT	