



¹ d ₁	² d ₂	b	d ₃	d ₄	d ₅	h ₁	h ₂ ≈	t min.
40	M 4	4	11	11,8	7	22	4	8
50	M 5	5	13	13,8	9	28	5	10
63	M 6	7	16	16,8	12	35	6	12

Specification

Wing nut

- Stainless steel precision casting AISI 316
- Matte finish (Ra < 0.8 µm) **MT**
- Polished finish (Ra < 0.8 µm) **PL**

Sealing ring

- H-NBR **H**
- EPDM **E**
- FKM **F**
- Operating temperature -25 °C to + 150 °C
- Operating temperature -40 °C to + 120 °C
- Operating temperature -5 °C to +200 °C
- FDA compliant material
- Blue
- Hardness 85 ±5 Shore A

RoHS

Wing nuts GN 8341 comply with the DGVU testing principles and are intended for use in hygienic areas. The versions with PL finish, as well as with sealing ring H and E are additionally certified according to the guidelines of the EHEDG. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

Wing nuts clamp and fasten parts easily without tools. The ergonomic shape allows for high tightening forces.

The wing nuts can also be used in particularly aggressive environments thanks to the material used.

see also...

	Page
GN 8340 Wing Nuts (Stainless Steel)	QVX
GN 8351 Wing Screws (Stainless Steel, Hygienic Design)	QVX
GN 5064 T-Handles (Stainless Steel, Hygienic Design)	QVX

Technical Information

Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 7600 Sealing Rings	QVX
-----------------------	-----

How to order

¹ d ₁	
² d ₂	
³ Finish	
⁴ Material (Sealing ring)	

GN 8341-50-M5-MT-E

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

