




- 2

Type
- T4

With square U-bolt, with catch
- T

Without square U-bolt, with catch

1

Size	F _H in N Holding capacity	a	b ₁	b ₂	b ₃	b ₄	b ₅	d ₁	d ₂	h ₁ ≈	h ₂
160	1600	5	26	35	21	25,5	14	M 4	4,3	40	10
320	3200	8	36	44	32	37	22	M 6	6,5	57,5	15
700	7000	13	52	54	38	48,5	26	M 8	8,5	82	23

Size	l ₁ ≈	l ₂ min.	m ₁	m ₂	m ₃	m ₄	m ₅	r ≈ at w ₂ = 0	s	w ₁ Stroke	w ₂ ≈ Adjustable range
160	104	4,5	22	6,5	13	6,5	14,3	52	2	32	10
320	159	6	25,5	8,5	19	10,5	20,5	78	3	53	21
700	225	8	36,5	10	32	13,5	27	102	3,5	64	25

Specification

- Parts in sheet metal
Case-hardened steel C10
Zinc plated, blue passivated
- Square U-bolt
Steel St. 37
Zinc plated, blue passivated
- All moving parts
Lubricated with special grease
- Handle with plastic cap
Red, oil resistant
- RoHS

Information

The stroke of the square U-bolt of latch type toggle clamps GN 851.2 can be adjusted within its range.

In the clamped position the square U-bolt and the clamping arm are horizontal to the vertical fixing plane.

In addition to the standard lengths of square U-bolts shown in the table, a variety of other lengths are also available under the GN 951.1 series.

see also...

- General Information for Toggle Clamps → Page 698
- Square U-Bolts GN 951.1 → Page 774

How to order

1

2

GN851.2-160-T4

1

Size

2

Type

