




	2	3										
For swing clamps Size	d ₁	m	a	b ₁	b ₂	b ₃	d ₂	d ₃	h ₁	h ₂	Length l	
16	8	41	15	4,3	6,7	12,5	M 4	5,5	9	5,5	50,6	
20	12	48	20	5,5	9,3	17	M 5	8,5	11	5,5	61,2	
25	14	50	20	6,5	11,3	18	M 6	8,5	16	6,5	64,6	
32 / 40	16	65	25	8,5	14,5	20	M 8	8,5	18	9	82,2	
50 / 63	20	85	30	10,5	17,5	25	M 10	10,5	23	10	106,2	

Specification

1

4

• Aluminum

Hard anodized

Wear-resistant surface

AL

HE

• Flanged washers

Steel, zinc plated, blue passivated

• Socket cap screw DIN 912

Steel, zinc plated, blue passivated

• Washer ISO 7092

Steel, zinc plated, blue passivated

• RoHS

Accessory

• Clamping Screws GN 708.1 → Page 812

Information

Clamping arms GN 875.2 with slotted hole designed as accessories to swing clamps GN 875 / GN 876. The slotted hole allows arbitrary positioning of application-specific pressing elements in connection with the two flanged washers.

The angle orientation of the clamping arm can be set arbitrarily during mounting on the swing clamp. When tightening the screw, the piston rod must not experience any torque. The clamping arm must therefore be held to prevent twisting.

Included are a socket cap screw DIN 912 and a washer ISO 7092 for fastening to the swing clamp as well as two flanged washers for fastening the clamping bolts.

see also...

• Swing Clamps GN 875 (in Block Version) → Page 842

• Swing Clamps GN 876 (with Screw-In Thread) → Page 844

How to order	1	Material
	2	d ₁
	3	m
	4	Finish
GN875.2-AL-16-65-HE		