



1.1

1.2

1.3

1.4

2.1

2.2

2.3

2.4

1

2

d ₁ ±0,2	Length l ±0,25						d ₂	for thread tapping screws DIN 7500
	194	244	294	394	-	-		
20	194	244	294	394	-	-	4,5	M 5
28	192	242	292	392	492	592	5,5	M 6
30	189	289	389	489	589	989	3,6	M 4

Specification

3

Aluminum

- Powder coated
Black, RAL 9005, textured finish (available up to 3000 mm length)
- Anodized, natural color (available up to 2600 mm length)

● SW

● EL

RoHS

On request

- Plastic cover in black or light gray for tube Ø 28

Handle tubes GN 930 with screw channel are designed for use in a variety of different tube handles (e.g. GN 333).

For applications not requiring handle bases, the screw channel provides a very economical fixing solution with thread-tapping screws. The lengths l listed in the table are ex stock lengths. Depending to the finish, any lengths until max. 3000 mm are available.

see also...

Page

GN 333 Tubular Handles

QVX

Accessory

GN 333.8 Handle Legs (for tubes Ø 28, angled)

QVX

GN 333.9 Handle Legs (for tubes Ø 28, straight)

QVX

How to order

GN 930-30-989-EL

1	d ₁
2	Length l
3	Finish

