


Mounting example



3 Type

- A** With bore for cap screw
- B** With threaded bore d_2

1

2

b Size of the slide	l₁	d₁ For socket cap screws DIN 912	d₂	h	l₂	l₃	l₄	l₅
30	41	2,7	M 2,5	4,2	35,4	41	35,4	6,5
50	67	3,3	M 3	7	58	67	58	10
80	105	4,5	M 4	12,5	92	105	92	14,5
120	145	5,5	M 5	13,8	131,8	145	131,8	14,5

Specification

- Aluminum
Anodized, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS

Information

Fastening units GN 900.1 are fitted to the base of the adjustable slide units GN 900 from the operator's side.

The mounting is made on the outside ledge of the slide so that the inner slide can still be moved.

A fastening unit GN 900.1 consists of two mounting rails. Four Stainless Steel-cap screws are included.

see also...

- *Adjustable Slide Units GN 900* → Page 1938

How to order

GN 900.1-80-105-A

- 1** b
- 2** l₁
- 3** Type