




Inox
Stainless
Steel

- 2

Bore code
- B

Without keyway
- K

With keyway DIN 6885-1 P9
- 4

Type
- A

Without handle
- D

With revolving handle

1			3							
d ₁	d ₂ H8 Bore		b	d ₃	l ₁	l ₂ ≈	l ₃ ≈	r	Ø Handle	No. of spokes
100	10	12	7	20	15	27,5	45	44	18	3
125	12	14	9	24	16	28,5	55	55	21	3
140	14	16	10	28	18	30,5	70,5	62	23	3
160	14	16	11	31	20	35,5	70,5	71	23	3
200	18	20	14	36	23	39	70,5	90	23	3

Specification

- Wheel body

Stainless steel precision casting AISI CF-8

• Hub machined

• Rim turned

• Matte shot-blasted
- Revolving handle similar to GN 598.1

Plastic, Phenolic resin (PF)

• Black, shiny finish

• Spindle

Stainless steel AISI 304

RoHS

The design of handwheels GN 949 complies with the requirements of hygiene standards.

The revolving handles are made of phenolic resin which, in general, provides good resistance to the impact of chemical agents.

Technical Information	Page
Keyways P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX
Accessory	
GN 184.5 Countersunk Washers (for axial fixation)	QVX

How to order

1

2

3

4

GN949-125-B12-A

1	d ₁
2	Bore code
3	d ₂
4	Type