



3 Type

- D With plain shaft
- E With threaded stud

2

| d ₁ | d ₂ h8 Type D | | d ₃ Type E | | d ₄ h13 | l ₁ ≈ | l ₂ | l ₃ | A/F Internal hex |
|----------------|-----------------------------|----|--------------------------|------|--------------------|------------------|----------------|----------------|---------------------|
| | ST / AL | KT | ST / AL | KT | | | | | |
| 16 | 7 | 7 | M 6 | M 6 | 10 | 49 | 11 | 5,5 | 3 |
| 20 | 8 | 8 | M 8 | M 8 | 13 | 61 | 13 | 6 | 4 |
| 25 | 10 | 10 | M 10 | M 10 | 16 | 75 | 14 | 8 | 5 |
| 32 | 13 | 13 | M 12 | M 12 | 20 | 95 | 21 | 10,5 | 6 |
| 36 | 16 | - | M 16 | - | 22 | 106 | 26 | 11 | 8 |

Specification

Handle

- Steel
- Zinc plated, blue passivated
- Aluminum
- Glossy finish
- Plastic, Polyamide (PA)
- Operating temperature up to 110 °C
- Black, matte finish

1

ST

AL

KT

Revolving handles DIN 98 type D are supplied unassembled so that the shaft can be press fitted or screwed into a tapped blind bore prior to assembly. Light taps with a soft-head hammer in the axial direction affix the handle to the axle with sufficient firmness that it is held in place axially while still remaining turnable.

Technical Information

- ISO Fundamental Tolerances
- Plastic Characteristics

Page

- QVX
- QVX

Spindle

- Steel
- Zinc plated, blue passivated

RoHS

How to order

DIN 98-KT-32-D

- 1 Material
- 2 d₁
- 3 Type