







Standard	Shaft Ø in mm	Hub clamping	Rated torque in Nm	Misalignment			Zero backlash
				Axial	Lateral	Angular	
GN 2240 Page 1680 Elastomer jaw couplings	 3 - 25		0,7 - 60	x	x	x	
GN 2241 Page 1682 Elastomer jaw couplings	 3 - 25		0,7 - 60	x	x	x	
GN 2242 Page 1684 Oldham couplings	 4 - 20		1 - 28		x	x	
GN 2243 Page 1686 Oldham couplings	 2 - 20		0,5 - 28		x	x	
GN 2244 Page 1688 Bellows couplings	 5 - 19		1,5 - 10	x	x	x	x
GN 2246 Page 1690 Beam couplings	 4 - 12		0,3 - 4	x	x	x	x

Standard	Suitable for use with			Application examples	Special features
	Servo motors	Stepper motors	Universal motors		
GN 2240 Page 1680 Elastomer jaw couplings	x	x	x	- Hydraulic pumps - Packaging machines - Industrial robots - Fans - Agitators	- High torques - Fast and simple plug-in assembly
GN 2241 Page 1682 Elastomer jaw couplings	x	x	x		
GN 2242 Page 1684 Oldham couplings		x	x	- Conveyor systems - Packaging machines - Positioning drives - Pumps	- High torques - High lateral misalignment compensation - Fast and simple plug-in assembly
GN 2243 Page 1686 Oldham couplings		x	x		
GN 2244 Page 1688 Bellows couplings	x	x		- Rotary encoders - Position measuring systems - Test benches - Industrial robots - Spindle drives	- Precise angle and torque transmission - High torsional stiffness
GN 2246 Page 1690 Beam couplings		x		- Confectionery machines - Industrial robots - CAT scanners - Position measuring systems	- Precise angle and torque transmission - Manufactured from a single piece - High torsional stiffness

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

