



b	d <sub>1</sub> F9					d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	m <sub>5</sub>
48	B 12	B 14	B 15	B 16	B 20	5,5	66,5	43	15	24,5	30	34	36	33,6	25	17

**Specification**

**Clamping plate**

- Zinc die casting
- Powder coated
- Black, textured finish

**Adjustable hand lever GN 302.1**

- Handle
  - Zinc die casting
  - Powder coated
  - Black, RAL 9005, textured finish
- Insert / Retaining screw
  - Stainless steel AISI 303

RoHS

Clamping plates GN 953.7 are used in connection with position indicators GN 953 / GN 953.2. The mounting holes support typical bore hole patterns. In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...	Page
GN 953 Position Indicators (Hollow Shaft Steel)	QVX
GN 953.2 Position Indicators (Hollow Shaft Stainless Steel)	QVX

**Technical Information**

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN953.7-48-B16

1	b
2	d <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

