




- 4

Type (Base plate)
- C3

Polished,
rubber vulcanized, black

1		2		3		3										3													
d ₁	d ₂	I ₁					Version T / TK					I ₂					Version V / VK					I ₃				Version W			
		Version S / SK																											
60	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
60	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
60	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
60	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	129	154	179	204										
80	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
80	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
80	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
80	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	131	156	181	206										
80	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	155	180	205	255										
80	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	179	229	279	-										
100	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
100	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
100	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
100	M 16	-	-	-	-	75	100	125	150	200	250	75	100	125	150	133	158	183	208										
100	M 20	-	-	-	-	75	100	125	150	200	250	100	125	150	200	157	182	207	257										
100	M 24	-	-	-	-	100	125	150	200	300	-	100	150	200	-	181	231	281	-										
120	M 20	-	-	-	-	75	100	125	150	200	250	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
120	M 24	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			
120	M 30	-	-	-	-	100	125	150	200	300	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-			

Specification

- Base plate
Stainless steel AISI 304

• Threaded stem
Stainless steel AISI 303

• Hex nut ISO 4032
Stainless steel AISI 304
- Rubber pad
Acrylonitrile butadiene rubber (NBR)

- Black

- FDA compliant

- Hardness 85±5 Shore A

- Vulcanized
- Load Rating Information → Page XYZ

• Plastic Characteristics → Page XYZ


• Stainless Steel Characteristics
→ Page XYZ

• RoHS


On request

• Rubber pad available
in various colors

Versions of threaded stem




5
S Without nut
SK With nut




5
T Without nut
TK With nut

External hex at the bottom at d₂ M 8, M 10, M 12

Wrench flat at the bottom at d₂ M 16, M 20, M 24, M 30



5
V Without nut
VK With nut



5
W With adjustable sleeve

External hex at the top and wrench flat at the bottom at d₂ M 16, M 20, M 24

Covered thread and wrench flat at the bottom at d₂ M 16, M 20, M 24

d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	l ₄	l ₅	l ₆	s	A/F ₁	A/F ₂	A/F ₄	A/F ₅	A/F ₆	w in °
60	M 8 M 10 M 12	-	31	-	-	-	-	-	2	17	-	-	-	-	32
60	M 16 - -	24	-	37	33	45	45	29	2	-	12	10	12	20	32
80	M 8 M 10 M 12	-	33	-	-	-	-	-	2	17	-	-	-	-	26
80	M 16 - -	24	-	39	35	45	45	29	2	-	12	10	12	20	26
80	M 20 - -	30	-	39	36	56	56	36	2	-	15	13	16	24	26
80	M 24 - -	35	-	41	38	67	67	42	2	-	19	17	20	30	26
100	M 8 M 10 M 12	-	35	-	-	-	-	-	2	17	-	-	-	-	22
100	M 16 - -	24	-	41	37	45	45	29	2	-	12	10	12	20	22
100	M 20 - -	30	-	41	38	56	56	36	2	-	15	13	16	24	22
100	M 24 - -	35	-	43	40	67	67	42	2	-	19	17	20	30	22
120	M 20 - -	-	-	43	-	-	-	-	2	-	15	-	-	-	20
120	M 24 - -	-	-	46	-	-	-	-	2	-	19	-	-	-	20
120	M 30 - -	-	-	50	-	-	-	-	2	-	24	-	-	-	20

Information

Leveling feet GN 17 are suitable for use in aggressive environments.

The inclined surfaces for liquid runoff and the high surface quality of the base plate simplify cleaning and prevent the accumulation of dust or dirt. The FDA compliant and vulcanised rubber underlay seals the base against the resting surface and allows the feet to be used in food-processing areas or the pharmaceutical industry, for example.

The leveling feet are supplied assembled and cannot be disassembled.

see also...

- [Leveling Feet GN 18 \(SST AISI 316L\)](#) → Page XYZ
- [Leveling Feet GN 19 \(SST, Hygienic Design\)](#) → Page XYZ
- [Leveling Feet GN 31 \(with Rubber Pad\)](#) → Page XYZ
- [Leveling Feet GN 33 \(with Mounting Flange\)](#) → Page XYZ
- [Leveling Feet GN 41 \(with / without Rubber Pad\)](#) → Page XYZ

How to order

1	d ₁
2	d ₂
3	l ₁ (l ₂ , l ₃)
4	Type (Base plate)
5	Version (Stud)

GN 17-80-M20-100-C3-T